



Areas of use for AESCULAP cutter heads

Dog breed	Short coat	Medium coat	Long coat
<b>Crossbreeds</b> Rear area Paws Body – clean coat Body – matted coat Legs	2mm – GH715/GT742 1mm – GH712 3mm – GT748 5mm – GT758 5mm – GT758	5mm – GT758 5mm – GT758 7mm – GT770 or 9mm - GT779	9mm - GT779 7mm – GT770 12-16mm – GT782/784
<b>Airedale</b> Rear area Paws Body – normal coat structure Head, body – clean coat Head, body – matted coat Legs Ears – outside/inside	2mm – GH715/GT742 2mm – GH715/GT742 Trimming 3mm – GT754 3mm – GT748 12-16mm – GT782/784 2mm – GH715/1mm – GH712	5mm – GT758 12-16mm – GT782/784	7mm – GT770 12-16mm – GT782/784
<b>Bearded Collie</b> Rear area Paws Body – clean coat Body – matted coat	2mm – GH715/GT742 1mm – GH712 Scissors 5mm – GT758	12mm – GT782 7mm – GT770	16mm – GT784 9mm - GT779
<b>Bedlington Terrier</b> Rear area Paws, face, tail Body/legs	2mm – GH715/GT742 1mm – GH712 3mm – GT754	2mm – GH715/GT742 5mm – GT758	7mm – GT770 or 9mm – GT779
<b>Bichon Frise</b> Rear area Paws Body – clean coat Body – matted coat	2mm – GH715/GT742 1mm – GH712 9mm – GT779 5mm – GT758	12mm – GT782 7mm – GT770	16mm – GT784
<b>Bouvier des Flandres</b> Rear area Paws Body – clean coat Body – matted coat Head Ears – outside/inside	2mm – GH715/GT742 1mm – GH712 9mm – GT779 5mm – GT758 3mm – GT754 2mm – GH715/1mm – GH712	12mm – GT782 7mm – GT770	16mm – GT784 9mm – GT779



<b>Briard</b> Rear area Paws Body – clean coat Body – matted coat	2mm – GH715/GT742 1mm – GH712 9mm – GT779 3mm – GT754	12mm – GT782 5mm – GT758	16mm – GT784 7mm – GT770
<b>Cairn Terrier</b> Rear area Paws Body – normal coat structure Body – matted coat structure	2mm – GH715/GT742 1mm – GH712 Trimming 3mm – GT754	2mm – GH715/GT742 5mm – GT758	7mm – GT770
<b>Cocker Spaniel</b> <b>American</b> Paws Rear area Face, head, ear base Body – clean coat (plucking) Body – matted coat <b>English</b> Paws Rear area Face, head, ear base Body – clean coat (plucking) Body – matted coat	1mm – GH712 2mm – GH715/GT742 3mm – GT754 3mm – GT748 3mm – GT748 1mm – GH712 2mm – GH715/GT742 3mm – GT754 3mm – GT748 3mm – GT748	5mm – GT758 5mm – GT758 2mm – GH715/GT742 5mm – GT758	7mm – GT770 7mm – GT770
<b>English, Irish, Gordon Setter</b> Rear area Paws Head, face, ear base Body – clean coat (plucking) Body – matted coat	2mm – GH715/GT742 1mm – GH712 3mm – GT748 5mm – GT758 5mm – GT758	7mm – GT770	9mm – GT779
<b>English Springer Spaniel</b> Rear area Paws Head Body – clean coat (plucking) Body – matted coat	2mm – GH715/GT742 1mm – GH712 3mm – GT754 5mm – GT758 5mm-GT758	7mm – GT770	9mm – GT779
<b>Irish Terrier</b> Rear area Head Body – normal coat structure Body	2mm – GH715/GT742 3mm – GT754 Trimming 3mm – GT754	5mm – GT758	7mm – GT770
<b>Kerry Blue Terrier</b> Rear area Paws Head Ears – outside/inside Body – clean coat structure Body – matted coat structure Legs	2mm – GH715/GT742 1mm – GH712 3mm – GT754 2mm – GH715/1mm – GH712 3mm – GT754 3mm – GT754 7mm – GT770	5mm – GT758 5mm – GT758 9mm – GT779	7mm – GT770 16mm – GT784



<b>Lakeland Terrier</b> Rear area Paws Head Ears – outside/inside  Body – normal coat structure Body – clean coat	2mm – GH715/GT742 1mm – GH712 3mm – GT754 2mm – GH715/1mm – GH712 Trimming 3mm – GT754	5mm – GT758	7mm – GT770
<b>Lhasa Apso</b> Rear area Paws Clean coat Matted coat	2mm – GH715/GT742 1mm – GH712 9mm – GT779 5mm – GT758	12mm – GT782  7mm – GT770	 16mm – GT784
<b>Old English Sheepdog</b> Rear area Paws Clean coat Matted coat	2mm – GH715/GT742 1mm – GH712 9mm – GT779 3mm – GT748	12mm – GT782 5mm – GT758	16mm – GT784 7mm – GT770
<b>Doodle</b> Rear area Paws Body – matted coat Body – clean coat	2mm – GH715/GT742 1mm – GH712 5mm – GT758 9mm – GT779	7mm – GT770 12mm – GT782	16mm – GT784
<b>Pekingese</b> Rear area Paws Clean coat Matted coat	2mm – GH715/GT742 1mm – GH712 9mm – GT779 5mm – GT758 or 3mm – GT748	12mm – GT782 7mm – GT770	16mm – GT784
<b>Portuguese Water Dog</b> Rear area Paws Body – clean coat Body – matted coat	2mm – GH715/GT742 1mm – GH712 9mm – GT779 3mm – GT748	12mm – GT782 5mm – GT758	7mm – GT770



<p><b>Schnauzer</b> Normal coat structure <b>Giant/Standard/Miniature</b> Rear area Paws Head, cheeks Ears – outside/inside</p> <p>Body Chest</p>	<p>Trimming 2mm – GH715/GT742 1mm – GH712 3mm – GT748 2mm – GH715/1mm – GH712 3mm – GT748 5mm – GT758 or 7mm – GT770 against the grain</p>	<p>5mm – GT758</p>	
<p><b>Scottish Terrier</b> Rear area Paws Normal coat structure, trimming Body Ears – outside/inside</p> <p>Head Chest</p>	<p>2mm – GH715/GT742 1mm – GH712 5mm – GT758 2mm – GH715/1mm – GH712 3mm – GT748 5mm – GT758</p>	<p>7mm – GT770</p>	
<p><b>Sealyham Terrier</b> Rear area Paws Body Head Ears – outside/inside</p>	<p>2mm – GH715/GT742 1mm – GH712 3mm – GT748 3mm – GT748 2mm – GH715/1mm – GH712</p>	<p>5mm – GT758</p>	<p>7mm – GT770</p>
<p><b>Welsh Terrier</b> Rear area Paws Body – normal coat structure Body Head Ears – outside/inside</p>	<p>2mm – GH715/GT742 1mm – GH712 Trimming 3mm – GT748 3mm – GT748 2mm – GH715/1mm – GH712</p>	<p>5mm – GT758</p>	<p>7mm – GT770</p>
<p><b>West Highland White Terrier</b> Normal coat structure, trimming Rear area Paws Body Head Tips of ears – outside/inside</p>	<p>2mm – GH715/GT742 1mm – GH712 5mm – GT758 3mm – GT748 2mm – GH715/1mm – GH712</p>	<p>7mm – GT770</p>	



<b>Wheaten Terrier</b> <b>Rear area</b> <b>Paws</b> Body, tail – clean coat Body, tail – matted coat Head Ears – outside/inside	2mm – GH715/GT742 1mm – GH712 9mm – GT779 5mm – GT758 3mm – GT748 2mm – GH715/1mm – GH712	12mm – GT782 7mm – GT770	
<b>Wire Fox Terrier</b> Rear area Paws Body – normal coat structure Body Head Ears – outside/inside	2mm – GH715/GT742 1mm – GH712 Trimming 3mm – GT748 3mm – GT748 2mm – GH715/1mm – GH712	5mm – GT758	7mm – GT770
<b>Yorkshire Terrier</b> Rear area Paws Body Head Tips of ears – outside/inside	2mm – GH715/GT742 1mm – GH712 9mm – GT779 3mm – GT748 2mm – GH715/1mm – GH712	12mm – GT782	16mm – GT784